


MultiFlex Floor Magnifier Instructions







MultiFlex Floor Magnifier Instructions

INSERTING BATTERIES








SPECIFICATIONS

Lamp	COB LED x 2 (6000K)	Lens Material	Acrylic
Lumens (high/low) – battery mode	200 - 20 LM	Magnification	
Lumens – 110v adapter	500 - 50 LM	• Lens	X2.5
Smart Dimmer	Variable memory setting	• Inset	X6
Battery Type	D Cell x3 (not incl)	Lens Dimensions	6" x 4"
AC Adapter	ETL#: 5003784	Magnifier Dimensions	11" x 9" x 53"
• Input	AC100 - 240 V, 50 - 60 HZ	Magnifier Weight	8.5 lb
• Output	5V DC, 2A		

USING THE AC ADAPTER



No tools required

Operation

• Press power button to turn lamp on and off

Smart Dimmer

- Press and hold power button
- Light will flash once at highest setting and again at lowest
- · Release power button at desired illumination level
- · Smart dimmer will remember light level until it is reset

Assembly

Please review instructions carefully before assembling the magnifier. To avoid damage, perform all work on a carpeted or padded surface. If you have questions or need assistance, please contact us at:

Email: info@lighitled.com *or* **Phone:** (503) 274-1227

Note: Remove all protective washers before installing the poles.

Care & Maintenance

- ✓ Clean magnifier with a soft, dry microfiber cleaning cloth
- ✓ If necessary, use an approved acrylic eyeglass cleaner
- × Do not expose lens to direct sunlight (fire hazard!)
- × Do not look directly into the light.
- × Indoor Use only
- × Do not mix battery types and use new batteries

Note: Using harsh chemicals or dirty cloths may scratch the lens.