

尺寸：285x210mm, 对折

正面

BFTLPT-1010

(In the Car)

Camping
& Outdoor

Elderly


On the
boat

24L


背面

EASY TO CARRY


■ HOW TO USE




1. Open the cap of water holding tank, fill the fresh water



2. Press the button and pull out slide valve at the same time, then open the seat cover before use




3. Close the seat cover, pull up and press down hand pump one or more times to rinse thoroughly by water after use




4. Close the slide valve by pushing fully for next use
PS: When the water level of the waste holding tank exceeds 12L, the indicator will turn to red

EASY TO CLEAN


■ HOW TO CLEAN




2. Press the detached button to separating the water holding tank and waste holding tank



- 1.Keep the slide valve and seat cover closed



3. Rotating the waste pipe, then remove cap and pour waste into permanent toilet facility



4. Rinse repeatedly after add fresh water or detergent, then pour rinse water into permanent toilet facility