


ORO

Design Vistosi

ORO SP P



The use of the horizontal inner membrane divides the transparent glass into two halves. The artisanal processing of the membrane makes each piece unique by varying the effect on the surface depending on the curvature of the membrane. Black nickel or glossy brass metal parts.



ORO SP P

TECHNICAL DATA:



CERTIFICATIONS:

LIGHT SOURCES

1x60 W 120V/60HZ G9

VOLUME Mc 0,04
GROSS WEIGHT Kg 3
NET WEIGHT Kg 1,5

download




SHADE FINISHING



CRBC

CRTR

FRAME FINISHING



NN

OG