

Cake machine instructions

characteristic:

The wheeled machine is beautiful in appearance and is coated with powder. The spatula is made of 304 stainless steel, and the turntable is made of high-quality aluminum alloy. Easy to operate, good performance. Wheels rotate smoothly, low noise, the rotation direction can be switched clockwise or counterclockwise. Single-phase three-line connection, with leakage protection device, safe and reliable operation.

Specifications: 500 / 350 / 570mm


Plug and voltage: triangle flat, 220v/110v

Material: metal + stainless steel spatula + aluminum alloy

Motor: DC brushless motor

Rotary table diameter: 35 cm, power: 200 W speed: 0-300 rpm Rotation direction: clockwise and counterclockwise, noise: less than 60 dB, weight: 24 kgLCD module

description:



Instructions for the use of equipment:

Put the cake embryo right

Adjust the distance of the vertical knife

Adjust turntable number (60-80)

Apply cream evenly

Shake the top wheel to adjust the horizontal knife down to collect the cake at right angles

The vertical knife is removed and the embryo is finished