
规格 270*240mm 材质128g 铜版纸



Introduction

Thank you for choosing to Floor Lamp, Please read this usermanual carefully and keep it for future reference, If you need any assistance, please contact us by email with your Amazon order number.

Specification

Model	MF18559.XIII
Material	Metal+ PC+Fabric
Power For Lamp	MAX 60W
Power For Blub	8W
Luminous Flux	1000lm
Color Temperature	3000K- 6000K
Lifespan	>30,000Hrs
Bulb Input Voltage	AC120V 60 Hz
Switch Style	Foot Switch

1 / Page

1 hour Timer


Color Temperature-

Working Mode

Color Temperature Setting

3000K,4000K,6000K

Product Size




2 / Page

Usage

There are two ways to control: Foot switch control or Remote control

Foot Switch

Tap the pedal switch with your foot to toggle ON/OFF.



Pairing the remote control with the lamp?

- 1. Tap the foot switch on/off 5 times continously till the bulb flash.
- 2. Tap the foot switch to turn off the flashing bulb.
- 3.Press and hold the remote's $\textcircled{\textbf{6}}$ button until the remote-control light flashes.
- 4. Tap the foot switch to turn on the lamp.
- 5.Press and hold the **(b)** button again. When the lamp bulb flashes the pairing is complete.

Clearing the pairing between the remote control and the bulb?

- 1. Make sure the lamp is plugged in and the bulb is off.
- 2. Tap the foot switch five (5) times.
- 3. When the lamp bulb flashes the pairing has been cleared.

Product Care

ON/OFF

-Brightness+

Brightness-

Night Light Mode

Breastfeed Mode

Reading Mode

(Q)

Œ

-☆+

- Please do not bend violently the lamp head to avoid damage when adjusting the angle of the lamp.
- Please read the user manual before use.
- Indoor use only. It is non waterproof .Do not use this product in humid environments or at high temperatures.
- Cut off the power when cleaning it or not using it.
- Do not use it exceed the voltage, the proper voltage for US is AC120V.60Hz.
- Stop using immediately if there is any defective issues found in the product.

Guarantee

Our standing floor lamp is guaranteed with 12 months product warranty which start from the purchase day.

For questions, assistance or suppport, please contact our customer service email with your order number and product model number For replacement, please also provide us your contact info including Name/Address/Cellphone# (For shipping usage only) , thank you for shopping with us.



Installation

