



FLEXSTONE
LUXURIOUS BATH SURROUNDS

Floating Seat Install Instructions

*** Read all instructions before starting ***

For missing items do not return to store.

Please call 877-941-3662


(Monday – Friday 8:00 a.m. – 5:00 p.m MT)

**For additional information and resources, visit:
www.FlexstoneProducts.com**


Floating Seat Instructions

Installation of Floating Seat


1. Install the Floating Seat after the FlexStone wall panels are installed. Be sure to remove the protective masking from the walls before installing the Floating Seat. Select the desired location for placement of the seat that is a comfortable position for sitting (typically around 18 inches from the floor).



2. Perform a dry fit to make sure the Floating Seat fits snugly into the corner of the wall surround. You will be able to fill in any small gaps between the seat and the wall panel with silicone in Step 6.




3. Apply Performance Pro adhesive to the foam on the backside of the seat using Hershey kiss sized beads of adhesive spaced approximately every 2 ½". Be sure to avoid the edge of the seat so that adhesive does not squeeze out and create a mess when installing.




4. Run a bead of Performance Pro 100% Silicone to the back corner of the Floating Seat, along the edge that will be placed into the back corner of the shower.

5. Install the Floating Seat at the desired location by simply pressing the seat firmly into the corner of the walls. Use masking tape to help hold in place while curing. Wait at least 72 hours before proceeding to step 6. This will allow the adhesive time to set up so the corner seat can remain steady while silicone is applied.



6. Seal all edge joints with Performance Pro 100% Silicone, as with the rest of the surround.



Please inspect package for any damage and read instructions carefully prior to installation. If you have any questions or issues, please call our customer support line at 877-941-3662.



FLEXSTONE WALL
PANELS ARE
¼ IN. THICK.